


The quick instruction of DK-HB1 Nightvision


DESCRIPTION OF COMPONENT:

- Right:** Make numerical adjustments in the menu, Electronic amplification
- ← Left:** Make numerical adjustments in the menu, Electronic amplification
- S key**
Photograph(p13)
Video recording(P16)
Playback(P14)
Function selection
- IR key**
Auxiliary illuminator(P10)
Screen brightness adjustment(p10)
Time set(p17)
Photo or video deletion(p18)
- ⏻ key**
Power management (Long press 5 seconds) (P8)
Function to confirm/ Video display or stop(p14)

OPERATING INSTRUCTION:



THE ATTACHMENT INSTRUCTION:



PERFORMANCE PARAMETER :

magnification	5	Operating voltage	
Objective lens diameter	Φ40mm	Viewing distance in low light	2m~∞
File of view	5°x3.75°	Replaceable battery	14500 rechargeable lithium battery
Ocular lens adjustment scope	±0.6	Viewing distance in low light	~200m
Dimension (L×W×H)	200x86x56mm	weight	400g

Notice:

The battery is chosen one 750mAh(Diameter 14mm, height 50mm) rechargeable lithium battery(It is recommended to use original factory supplied batteries).
When installing the battery, please push the battery cover in place to ensure the normal operation of the machine

The design and firmware of this product may change for development purposes.
The latest version of this manual is available from www.trgdtc.cn

P1S-0540
P15S-0540
CEFC
RoHS
2019.10



DSE